



Figure similar

MLFB-Ordering data 6FC5211-0BA01-0AA4

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Ambient conditions	
Input voltage	DC 24 V	Climate class according to EN60721-3-3 Condensation and icing excluded. Low air temperature 0 °C (32 °F).	
Power consumption, max.	30.2 W		
Mechanical data		Ambient temperature	
Degree of protection	IP20 / UL open type	Operation	0 ... 55 °C (32 ... 131 °F)
Net weight	1.50 kg (3.31 lb)	Transport	-40 ... 70 °C (-40 ... 158 °F)
Width	48.5 mm (1.91 in)	Storage	-20 ... 55 °C (-4 ... 131 °F)
Height	325.0 mm (12.80 in)	Relative humidity	
Depth	154.4 mm (6.08 in)	Operation	5 ... 95 %
		Storage	5 ... 95 %
		Transport	5 ... 95 %
Approvals			
Certificate of suitability		CE / UL / CSA	