



Figure similar

MLFB-Ordering data

6FC5303-0AF14-0AA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Screen		Ambient conditions	
Screen diagonal	15.6 in LCD color	Climate class according to EN60721-3-3 Condensation and icing excluded. Low air temperature 0 °C (32 °F).	
Screen resolution	1366 x 768 Pixel		
Rated data		Ambient temperature	
Input voltage	DC 24 V	Operation on the front	0 ... 45 °C (32 ... 113 °F)
Power consumption		Operation at the rear	0 ... 55 °C (32 ... 131 °F)
		Storage	-20 ... 55 °C (-4 ... 131 °F)
Maximum	42.0 W	Transport	-20 ... 55 °C (-4 ... 131 °F)
Standard	24.0 W	Relative humidity	
Mechanical data		Operation	5 ... 95 %
Net weight	7.0 kg (15.43 lb)	Storage	5 ... 95 %
Width	483.0 mm (19.02 in)	Transport	5 ... 95 %
Height	310.0 mm (12.20 in)	Approvals	
Depth	48.0 mm (1.89 in)	Certificate of suitability	CE / cULus
Installation depth	37.0 mm (1.46 in)		
	Clearance + 10 mm (0.39 in)		
Mounting surface			
Cutout width	450.0 mm (17.72 in)		
Cutout height	290.0 mm (11.42 in)		
Degree of protection			
Front side	IP65/IP66		
Rear side	IP20 / UL open type		