



Figure similar

MLFB-Ordering data

6FC5303-0AF17-0AA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Screen		Ambient conditions	
Screen diagonal	18.5 in LCD color	Climate class according to EN60721-3-3 Condensation and icing excluded. Low air temperature 0 °C (32 °F).	
Screen resolution	1366 x 768 Pixel		
Rated data		Ambient temperature	
Input voltage	DC 24 V	Operation on the front	0 ... 45 °C (32 ... 113 °F)
Power consumption		Operation at the rear	0 ... 55 °C (32 ... 131 °F)
		Storage	-20 ... 55 °C (-4 ... 131 °F)
Maximum	42.0 W	Transport	-40 ... 70 °C (-40 ... 158 °F)
Standard	24.0 W	Relative humidity	
Mechanical data		Operation	5 ... 95 %
Net weight	7.6 kg (16.76 lb)	Storage	5 ... 95 %
Width	483.0 mm (19.02 in)	Transport	5 ... 95 %
Height	337.0 mm (13.27 in)	Approvals	
Depth	64.9 mm (2.56 in)	Certificate of suitability	CE / cULus
Installation depth	56.0 mm (2.20 in)		
Clearance + 64 mm (2.52 in)			
Mounting surface			
Cutout width	465.0 mm (18.31 in)		
Cutout height	319.0 mm (12.56 in)		
Degree of protection			
Front side	IP65/IP66		
Rear side	IP20 / UL open type		