



Figure similar

MLFB-Ordering data 6FC5303-0AF35-3AA0

Client order no. :
Order no. :
Offer no. :
Remarks :
Item no. :
Consignment no. :
Project :

Rated data		Ambient conditions	
Input voltage	DC 5 V	Climate class according to EN60721-3-3 Condensation and icing excluded. Low air temperature 0 °C (32 °F).	
Power consumption, max.	5.0 W		
Mechanical data		Ambient temperature	
Net weight	0.795 kg (1.75 lb)	Operation on the front	0 ... 45 °C (32 ... 113 °F)
Width	265.0 mm (10.43 in)	Operation at the rear	0 ... 50 °C (32 ... 122 °F)
Height	230.0 mm (9.06 in)	Transport	-20 ... 60 °C (-4 ... 140 °F)
Depth	58.0 mm (2.28 in)	Storage	-20 ... 60 °C (-4 ... 140 °F)
Mounting surface		Relative humidity	
		Operation	5 ... 90 %
Degree of protection		Storage	5 ... 95 %
		Transport	5 ... 95 %
Cutout width	245.0 mm (9.65 in)	Approvals	
Cutout height	211.0 mm (8.31 in)	Certificate of suitability	CE / EAC
Rear side	IP00		
Front side	IP65		