



Figure similar

MLFB-Ordering data 6FC5303-0AP04-0AA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data		Ambient conditions	
Input voltage	DC 24 V	Climate class according to EN60721-3-3 Condensation and icing excluded. Low air temperature 0 °C (32 °F).	
Power consumption, max.	115.0 W		
Mechanical data		Ambient temperature	
Net weight	3.400 kg (7.50 lb)	Operation on the front	0 ... 45 °C (32 ... 113 °F)
Width	585.0 mm (23.03 in)	Operation at the rear	0 ... 55 °C (32 ... 131 °F)
Height	265.0 mm (10.43 in)	Transport	-40 ... 70 °C (-40 ... 158 °F)
Depth	55.0 mm (2.17 in)	Storage	-40 ... 70 °C (-40 ... 158 °F)
Installation depth	55.0 mm (2.17 in)	Relative humidity	
Mounting surface		Operation	5 ... 90 %
		Storage	5 ... 90 %
Cutout width	551.0 mm (21.69 in)	Transport	5 ... 90 %
Cutout height	231.0 mm (9.09 in)	Approvals	
Degree of protection		Certificate of suitability	CE / EAC / UL / UKCA
Rear side	IP00		
Front side	IP65		
	Key-operated switch IP54		