



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Electrical data		Mechanical data	
Operating voltage Up	DC 10 ... 30 V	Shaft version	Solid shaft
Max. power consumption	100 ... 300 mA (2.5 W)	Shaft diameter	10 mm
Interface	PROFIBUS DP-V2	Shaft length	20 mm
Clock input	Differential line receiver according to EIA Standard RS 485	Angular acceleration, max.	100000 rad/s ²
Data output	Differential line driver according to EIA Standard RS 485	Moment of inertia of rotor	0.00000190 kgm ²
Short-circuit strength	Yes	Vibration (55...2000 Hz), max.	100 m/s ²
Transmission rate	12 Mbit/s	Friction torque (at 20°C)	<= 0.01 Nm
LED for diagnostics	Yes (green/red)	Starting torque (at 20°C)	<= 0.01 Nm
Number of nodes	99	Net weight	0.5 kg
Connection type	Terminal block with address selector switch and bus terminating resistor in removable cover with radial cable glands (3 units), Radial	Speed max.	
Cable diameter	6.5 mm ... 9.0 mm, Tube dismantling possible without bus interruption	With ± 1 bit accuracy	5800 rpm
Resolution	27 bit, (8192 increments x 16384	Max. permissible speed (mech.)	6000 rpm
Telegram	According to PNO cncoder profile V4.1 Class1, Class 2, Class 3, standard telegram 81	Load capacity	
Cable length up to the subsequent electronics, max.		n <= 6000 rpm	
Up to 93.75 kbit/s	1200 m	- Axial	40 N
Up to 1.5 Mbit/s	200.0 m	- Radial at shaft end	110 N
Up to 12 Mbit/s	100.0 m	n > 6000 rpm	
Code type		- Axial	10 N
Sampling	Gray	- Radial at shaft end	20 N
Transmission	binary, PROFIBUS	Shock, max.	
		2 ms	2000 m/s ²
		6 ms	1000 m/s ²
		Degree of protection	
		Without shaft input	IP67
		With shaft input	IP64

MLFB-Ordering data 6FX2001-5QP24



Figure similar

Electrical data		Ambient temperature	
Parameterizability		During operation	-40 ... 85 °C
Preset	Yes	Standards	
Counting direction	Yes	Compliance with standards	CE, cULus
Resolution per revolution	Any 1 ... 8192	EMC class filter	Tested to DIN EN 50081 and EN 50082
Total resolution	Any 1 ... 8192 x 16384		
Speed signal	Yes		
Limit switch	Yes, 2 pieces		
Clock synchronism	Yes		
Slave-to-slave communication	Yes		
Accuracy	± 79 " with 8192 increments (± 1/2 LSB)		