

Data sheet for MICROMASTER Basic Operator Panel (BOP)

Article No. : 6SE6400-0BP00-0AA1

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :




Figure similar

Screen

Display design	LCD, monochrome
----------------	-----------------

Mechanical data

Degree of protection	IP20 / UL open type
Net weight	0.300 kg (0.66 lb)

Dimensions

Width	71.00 mm (2.80 in)
Height	80.00 mm (3.15 in)
Depth	16.00 mm (0.63 in)

Ambient conditions

Ambient temperature

Operation	-10 ... 50 °C (14 ... 122 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)
Transport	-40 ... 70 °C (-40 ... 158 °F)

Relative humidity at 25°C during

Max. operation	95 %
----------------	------

Approvals

Certificate of suitability	UL, CE, C-Tick (RCM)
----------------------------	----------------------