

MLFB-Ordering data                      6SE6400-3CC04-4DD0



Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

Rated data		Connections	
Input		Line side	
Number of phases	3 AC	Version	screw-type terminal
Line voltage	380 ... 600 V	Conductor cross-section	10.00 ... 16.00 mm² (8 ... 6 AWG)
Output		Load side	
Rated current	45.8 A	Version	Pigtail
Mechanical data		Conductor cross-section	16.00 mm² (6 AWG)
Dimensions		Cable length	0.79 m (2.59 ft)
Width	275.0 mm (10.8 in)	PE connection	
Height	520.0 mm (20.5 in)	Version	M8 stud
Depth	83.5 mm (3.3 in)	Standards	
Degree of protection	IP20 / UL open type	Compliance with standards	cURus
Net weight	13.0 kg (28.7 lb)		