

Data sheet for braking resistor

Article No. : 6SE6400-4BD12-0BA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Rated data

Rated power P _{DB}	0.2 kW
Rated power, max.	4 kW

General technical specifications

Resistance	160 Ω
DC-link voltage, max.	900 V

Mechanical data

Degree of protection	IP20 / UL open type
Net weight	1.6 kg (3.53 lb)
Dimensions	
Width	149 mm (5.87 in)
Height	239 mm (9.41 in)
Depth	43.5 mm (1.71 in)

Connections

Power connection	
Version	pigtail
Cable length	0.55 m (1.8 ft)
PE connection	
Version	pigtail
Version on housing	M4 stud bolt

Thermostatic switch

Version	Normally closed contact
Input current, max.	2.5 A
Conductor cross-section	2.5 mm² (AWG 14)