

MLFB-Ordering data 6SL3005-0DG41-6AA7

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Rated data

Input	
Number of phases	3 AC
Line voltage	500 ... 690 V

Output	
Rated current	1560.0 A

Mechanical data

Dimensions	
Width	440.0 mm (17.3 in)
Height	705.0 mm (27.8 in)
Depth	580.0 mm (22.8 in)
Degree of protection	IP00
Net weight	365.0 kg (14.4 lb)