

Data sheet for Line filter

Article No. : 6SL3000-0BE36-0AA0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data	
------------	--

Input	
Number of phases	3 AC
Line voltage	380 ... 480 V
Output	
Rated current	600.0 A

General technical specifications	
----------------------------------	--

Power loss	0.055 kW
------------	----------

Mechanical data	
-----------------	--

Degree of protection	IP00
Net weight	19.00 kg (41.89 lb)
Dimensions	
Width	400.0 mm (15.75 in)
Height	265.0 mm (10.43 in)
Depth	140.0 mm (5.51 in)

Connections	
-------------	--

Line side	
Version	Flange connection for cable lug M10
Load side	
Version	Flange connection for cable lug M10
PE connection	
Version	1 x hole for M10

Standards	
-----------	--

Compliance with standards	cURus
---------------------------	-------