

Data sheet for Line filter

Article No. : 6SL3000-0BG34-4AA0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Input	
Number of phases	3 AC
Line voltage	500 ... 600 V
Output	
Rated current	440.0 A

General technical specifications

Power loss	0.047 kW
------------	----------

Mechanical data

Degree of protection	IP00
Net weight	12.30 kg (27.12 lb)
Dimensions	
Width	360.0 mm (14.17 in)
Height	240.0 mm (9.45 in)
Depth	116.0 mm (4.57 in)

Connections

Line side	
Version	1 x hole for M8
Load side	
Version	1 x hole for M10
PE connection	
Version	1 x hole for M8

Standards

Compliance with standards	cURus
---------------------------	-------