



Figure similar

Data sheet for braking resistor

Article No. : 6SL3000-1BE31-3AA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data	
Rated power P _{DB}	25 kW
Rated power, max.	125 kW

General technical specifications	
Resistance	4.4 Ω

Mechanical data	
Degree of protection	IP20 / UL open type
Net weight	50 kg (110.23 lb)
Dimensions	
Width	740 mm (29.13 in)
Height	605 mm (23.82 in)
Depth	485 mm (19.09 in)

Connections	
Power connection	
Version	M10 screw studs

Thermostatic switch	
Version	Normally closed contact
Input current, max.	2.5 A