



Figure similar

Data sheet for braking resistor

Article No. : 6SL3000-1BE32-5AA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Rated power P _{DB}	50 kW
Rated power, max.	250 kW

General technical specifications

Resistance	2.2 Ω
------------	-------

Mechanical data

Degree of protection	IP20 / UL open type
Net weight	120 kg (264.55 lb)
Dimensions	
Width	810 mm (31.89 in)
Height	1,325 mm (52.17 in)
Depth	485 mm (19.09 in)

Connections

Power connection	
Version	M10 screw studs

Thermostatic switch

Version	Normally closed contact
Input current, max.	2.5 A