



Figure similar

Data sheet for braking resistor

Article No. : 6SL3000-1BE32-5AA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

| | |
|-----------------------------|--------|
| Rated power P _{DB} | 50 kW |
| Rated power, max. | 250 kW |

General technical specifications

| | |
|------------|-------|
| Resistance | 2.2 Ω |
|------------|-------|

Mechanical data

| | |
|----------------------|---------------------|
| Degree of protection | IP20 / UL open type |
| Net weight | 120 kg (264.55 lb) |
| Dimensions | |
| Width | 810 mm (31.89 in) |
| Height | 1,325 mm (52.17 in) |
| Depth | 485 mm (19.09 in) |

Connections

| | |
|------------------|-----------------|
| Power connection | |
| Version | M10 screw studs |

Thermostatic switch

| | |
|---------------------|-------------------------|
| Version | Normally closed contact |
| Input current, max. | 2.5 A |