

MLFB-Ordering data 6SL3000-2CE34-1AA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Number of phases	3 AC	Power connection Power Module	
Line voltage	380 ... 480 V	Version	flat connector for cable lug M10
Rated current	408.0 A	Conductor cross-section	240.00 mm²
Power loss	0.380 kW	Power connection motor	
		Version	Flange connection for cable lug M10
		Conductor cross-section	240.00 mm²
Mechanical data		Max. motor cable length	
Degree of protection	IP00	Shielded	300.00 m (984.25 ft)
Net weight	198.00 kg (436.52 lb)	Unshielded	450.00 m (1476.38 ft)
Dimensions		PE connection	
Width	620.0 mm (24.41 in)	Version	M10 screw
Height	370.0 mm (14.57 in)	Standards	
Depth	360.0 mm (14.17 in)	Certificate of suitability	cURus