

MLFB-Ordering data 6SL3000-2CE32-3AA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Number of phases		Power connection Power Module	
3 AC		Version	flat connector for cable lug M10
Line voltage		Conductor cross-section	
380 ... 480 V		185.00 mm² (AWG -5)	
Rated current		Power connection motor	
225.0 A		Version	Flange connection for cable lug M10
Power loss		Conductor cross-section	185.00 mm² (AWG -5)
0.350 kW		Max. motor cable length	
Electrical data		Shielded	300.00 m (984.25 ft)
Inductance		Unshielded	450.00 m (1476.38 ft)
0.35 mH		PE connection	
Capacitance		Version	M10 screw
28.20 µF		Standards	
Mechanical data		Certificate of suitability	cURus
Degree of protection			
IP00			
Net weight			
124.00 kg (273.37 lb)			
Dimensions			
Width			
620.0 mm (24.41 in)			
Height			
300.0 mm (11.81 in)			
Depth			
320.0 mm (12.60 in)			