

MLFB-Ordering data 6SL3000-2CE32-3AA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Number of phases		Power connection Power Module	
3 AC		Version	
Line voltage		flat connector for cable lug M10	
380 ... 480 V		Conductor cross-section	
Rated current		185.00 mm² (AWG -5)	
225.0 A		Power connection motor	
Power loss		Version	
0.350 kW		Flange connection for cable lug M10	
Electrical data		Conductor cross-section	
Inductance		185.00 mm² (AWG -5)	
0.35 mH		Max. motor cable length	
Capacitance		Shielded	
28.20 µF		300.00 m (984.25 ft)	
Mechanical data		Unshielded	
Degree of protection		450.00 m (1476.38 ft)	
IP00		PE connection	
Net weight		Version	
124.00 kg (273.37 lb)		M10 screw	
Dimensions		Standards	
Width		Certificate of suitability	
620.0 mm (24.41 in)		cURus	
Height			
300.0 mm (11.81 in)			
Depth			
320.0 mm (12.60 in)			