

MLFB-Ordering data                      6SL3000-2CE32-8AA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Number of phases	3 AC	Power connection Power Module	
Line voltage	380 ... 480 V	Version	flat connector for cable lug M10
Rated current	276.0 A	Conductor cross-section	240.00 mm²
Power loss	0.400 kW	Power connection motor	
		Version	Flange connection for cable lug M10
		Conductor cross-section	240.00 mm²
		Max. motor cable length	
		Shielded	300.00 m (984.25 ft)
		Unshielded	450.00 m (1476.38 ft)
		PE connection	
		Version	M10 screw
Mechanical data		Standards	
Degree of protection	IP00	Certificate of suitability	cURus
Net weight	127.00 kg (279.99 lb)		
Dimensions			
Width	620.0 mm (24.41 in)		
Height	300.0 mm (11.81 in)		
Depth	320.0 mm (12.60 in)		