



Figure similar

MLFB-Ordering data 6SL3040-1NC00-0AA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Ambient conditions	
Input voltage	DC 24 V	Climate class according to EN60721-3-3 Condensation and icing excluded. Low air temperature 0 °C (32 °F).	
		Ambient temperature	
		Operation	0 ... 55 °C (32 ... 131 °F)
		Transport	-40 ... 70 °C (-40 ... 158 °F)
		Storage	-25 ... 55 °C (-13 ... 131 °F)
Mechanical data		Relative humidity	
Degree of protection	IP20 / UL open type	Operation	5 ... 95 %
Net weight	2.6 kg (5.69 lb)	Storage	5 ... 95 %
Width	25 mm (1.97 in)	Transport	5 ... 95 %
Height	414 mm (16.30 in)	Approvals	
Depth	272 mm (10.71 in)	Certificate of suitability	CE, cULus