

Data sheet for Line filter

Article No. : 6SL3203-0BE23-5HA0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data	
Input	
Number of phases	3 AC
Line voltage	200 ... 480 V
Output	
Rated current	35.0 A
Mechanical data	
Degree of protection	IP20 / UL open type
Net weight	2.30 kg (5.07 lb)
Dimensions	
Width	50.0 mm (1.97 in)
Height	296.2 mm (11.66 in)
Depth	220.0 mm (8.66 in)

Connections	
Line side	
Version	screw-type terminal
Conductor cross-section	0.50 ... 10.00 mm² (AWG 21 ... AWG 8)
Load side	
Version	Screw-type terminals
Conductor cross-section	16.00 mm² (AWG 6)
PE connection	
Version	M4 screw studs
Standards	
Compliance with standards	CE, cURus, EAC