



Figure similar

MLFB-Ordering data

6SL3210-5DE12-4UA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Ambient conditions	
Input		Cooling	
Number of phases	3 AC	natural convection	
Line voltage	380 ... 480 V -15 % +10 %	Installation altitude	
Line frequency	45 ... 66 Hz	1000 m	
Output		Cooling air requirement	
Rated power	0.40 kW	0.005 m³/s (0.177 ft³/s)	
Rated current (IN)	1.20 A	Ambient temperature	
Max. output current	3.60 A	Operation	
Electronic power supply		0 ... 45 °C (32 ... 113 °F)	
Power supply	24 V ±10 %	Storage	
General tech. specifications		-40 ... 70 °C (-40 ... 158 °F)	
Power loss	36.00 W	Transport	
Connections		-40 ... 70 °C (-40 ... 158 °F)	
Motor end		Relative humidity	
Conductor cross-section	1.5 mm²	Max. operation	
Mechanical data		90 %	
Degree of protection	IP20 / UL open type	Standards	
Frame size	FSA	Compliance with standards	
Net weight	1.85 kg (4.08 lb)	CE	
Width	80.0 mm (3.15 in)		
Height	180.0 mm (7.09 in)		
Depth	200.0 mm (7.87 in)		