



Figure similar

MLFB-Ordering data

6SL3210-5DE21-4UA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data		Ambient conditions	
Input		Cooling	Forced-air cooling via fan
Number of phases	3 AC	Installation altitude	1000 m
Line voltage	380 ... 480 V -15 % +10 %	Cooling air requirement	0.005 m³/s (0.177 ft³/s)
Line frequency	45 ... 66 Hz	Ambient temperature	
Output		Operation	0 ... 45 °C (32 ... 113 °F)
Rated power	3.50 kW	Storage	-40 ... 70 °C (-40 ... 158 °F)
Rated current (IN)	11.00 A	Transport	-40 ... 70 °C (-40 ... 158 °F)
Max. output current	33.00 A	Relative humidity	
Electronic power supply		Max. operation	90 %
Power supply	24 V ±10 %	Standards	
General tech. specifications		Compliance with standards	CE
Power loss	54.00 W	Connections	
Motor end		Mechanical data	
Conductor cross-section	2.5 mm²	Degree of protection	IP20 / UL open type
		Frame size	FSC
		Net weight	5.65 kg (12.46 lb)
		Width	140.0 mm (5.51 in)
		Height	260.0 mm (10.24 in)
		Depth	240.0 mm (9.45 in)