



Figure similar

MLFB-Ordering data

6SL3210-5FE13-5UA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Ambient conditions	
Input		Cooling	Fan
Number of phases	3 AC	Installation altitude	1000 m
Line voltage	380 ... 480 V +10 % -15 %	Ambient temperature	
Line frequency	45 ... 66 Hz	Operation	0 ... 45 °C
Output		Storage	-40 ... 70 °C
Rated power	3.50 kW	Relative humidity	
Rated current (IN)	11.00 A	Max. operation	90 %
Max. output current	33.00 A	Standards	
Inputs / outputs		Compliance with standards	CE, KC, cULus, EAC, C-Tick (RCM)
Standard digital inputs		Communication	
Number	10	Communication	USS, Modbus RTU
Digital outputs			
Number	6		
Analog inputs			
Number	2		
Analog outputs			
Number	2		
Mechanical data			
Degree of protection	IP20 / UL open type		
Frame size	FSC		
Net weight	5.65 kg		
Width	140.0 mm		
Height	260.0 mm		
Depth	240.0 mm		