



Figure similar

MLFB-Ordering data

6SL3210-5FE13-5UA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

| Rated data              |                           | Ambient conditions        |                                  |
|-------------------------|---------------------------|---------------------------|----------------------------------|
| Input                   |                           | Cooling                   | Fan                              |
| Number of phases        | 3 AC                      | Installation altitude     | 1000 m                           |
| Line voltage            | 380 ... 480 V +10 % -15 % | Ambient temperature       |                                  |
| Line frequency          | 45 ... 66 Hz              | Operation                 | 0 ... 45 °C                      |
| Output                  |                           | Storage                   | -40 ... 70 °C                    |
| Rated power             | 3.50 kW                   | Relative humidity         |                                  |
| Rated current (IN)      | 11.00 A                   | Max. operation            | 90 %                             |
| Max. output current     | 33.00 A                   | Standards                 |                                  |
| Inputs / outputs        |                           | Compliance with standards | CE, KC, cULus, EAC, C-Tick (RCM) |
| Standard digital inputs |                           | Communication             |                                  |
| Number                  | 10                        | Communication             | USS, Modbus RTU                  |
| Digital outputs         |                           |                           |                                  |
| Number                  | 6                         |                           |                                  |
| Analog inputs           |                           |                           |                                  |
| Number                  | 2                         |                           |                                  |
| Analog outputs          |                           |                           |                                  |
| Number                  | 2                         |                           |                                  |
| Mechanical data         |                           |                           |                                  |
| Degree of protection    | IP20 / UL open type       |                           |                                  |
| Frame size              | FSC                       |                           |                                  |
| Net weight              | 5.65 kg                   |                           |                                  |
| Width                   | 140.0 mm                  |                           |                                  |
| Height                  | 260.0 mm                  |                           |                                  |
| Depth                   | 240.0 mm                  |                           |                                  |