

## Data sheet for SINAMICS V20

Article No. : 6SL3210-5BE31-8UV0



Figure similar

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

### Rated data

| Input                |                           |                               |
|----------------------|---------------------------|-------------------------------|
| Number of phases     | 3 AC                      |                               |
| Line voltage         | 380 ... 480 V -15 % +10 % |                               |
| Line frequency       | 47 ... 63 Hz              |                               |
| Output               |                           |                               |
| Number of phases     | 3 AC                      |                               |
| <b>Rated voltage</b> | <b>400V IEC</b>           | <b>480V NEC <sup>1)</sup></b> |
| Rated power (LO)     | 22.00 kW                  | 30.00 hp                      |
| Rated power (HO)     | 18.50 kW                  | 25.00 hp                      |
| Rated current (LO)   | 45.00 A                   | 40.00 A                       |
| Rated current (HO)   | 38.00 A                   | 34.00 A                       |
| Rated current (IN)   | 45.00 A                   |                               |
| Pulse frequency      | 4.00 kHz                  |                               |
| Output frequency     | 0 ... 550 Hz              |                               |

|                                                       |  |
|-------------------------------------------------------|--|
| Overload capability                                   |  |
| Low Overload (LO)                                     |  |
| 110 % rated output current for 60 s, cycle time 300 s |  |
| High Overload (HO)                                    |  |
| 150 % rated output current for 60 s, cycle time 300 s |  |

|                              |            |
|------------------------------|------------|
| General tech. specifications |            |
| Power factor λ               | 0.72       |
| Offset factor cos φ          | 0.95       |
| Efficiency η                 | 0.98       |
| Filter class (integrated)    | Unfiltered |

|               |                 |
|---------------|-----------------|
| Communication |                 |
| Communication | USS, Modbus RTU |

|                                    |                                             |
|------------------------------------|---------------------------------------------|
| Inputs / outputs                   |                                             |
| Standard digital inputs            |                                             |
| Number                             | 4                                           |
| Digital outputs                    |                                             |
| Number as relay changeover contact | 1                                           |
| Number as transistor               | 1                                           |
| Analog inputs                      |                                             |
| Number                             | 2 (Can be used as additional digital input) |
| Analog outputs                     |                                             |
| Number                             | 1                                           |

### Ambient conditions

|                         |                                |
|-------------------------|--------------------------------|
| Cooling                 | External fan                   |
| Installation altitude   | 1,000 m (3,280.84 ft)          |
| Ambient temperature     |                                |
| Operation <sup>2)</sup> | -10 ... 60 °C (14 ... 140 °F)  |
| Storage                 | -40 ... 70 °C (-40 ... 158 °F) |
| Relative humidity       |                                |
| Max. operation          | 95 %                           |

### Connections

|                         |                   |
|-------------------------|-------------------|
| Max. motor cable length |                   |
| Shielded                | 50 m (164.04 ft)  |
| Unshielded              | 100 m (328.08 ft) |

### Mechanical data

|                      |                                                               |
|----------------------|---------------------------------------------------------------|
| Mounting position    | Through-hole mounting / wall mounting / side-by-side mounting |
| Degree of protection | IP20 / UL open type                                           |
| Frame size           | FSE                                                           |
| Net weight           | 6.24 kg (13.76 lb)                                            |

|            |                     |
|------------|---------------------|
| Dimensions |                     |
| Width      | 245.0 mm (9.65 in)  |
| Height     | 264.5 mm (10.41 in) |
| Depth      | 209.0 mm (8.23 in)  |


### Standards

|                           |                                         |
|---------------------------|-----------------------------------------|
| Compliance with standards | CE, cULus, C-Tick (RCM), KC             |
| CE marking                | EN 61800-5-1 /EN 60204-1 and EN 61800-3 |

Data sheet for SINAMICS V20

Article No. : 6SL3210-5BE31-8UV0

| Converter losses to IEC61800-9-2*                    |        |
|------------------------------------------------------|--------|
| Efficiency class                                     | IE2    |
| Comparison with the reference converter (90% / 100%) | 41.0 % |



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*calculated values

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 440V-480V

<sup>2)</sup>Please observe derating at temperatures of 40 °C or above