



Figure similar

MLFB-Ordering data

6SL3210-5DE21-3UA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Ambient conditions	
Input		Cooling	Forced-air cooling via fan
Number of phases	3 AC	Installation altitude	1000 m
Line voltage	380 ... 480 V -15 % +10 %	Cooling air requirement	0.005 m³/s (0.177 ft³/s)
Line frequency	45 ... 66 Hz	Ambient temperature	
Output		Operation	0 ... 45 °C (32 ... 113 °F)
Rated power	3.70 kW	Storage	-40 ... 70 °C (-40 ... 158 °F)
Rated current (IN)	12.90 A	Transport	-40 ... 70 °C (-40 ... 158 °F)
Max. output current	24.60 A	Relative humidity	
Electronic power supply		Max. operation	90 %
Power supply	24 V ±10 %	Standards	
Connections		Compliance with standards	CE
Motor end			
Conductor cross-section	4.0 mm²		
Mechanical data			
Degree of protection	IP20 / UL open type		
Frame size	FSC		
Net weight	5.05 kg (11.13 lb)		
Width	140.0 mm (5.51 in)		
Height	260.0 mm (10.24 in)		
Depth	240.0 mm (9.45 in)		