

Data sheet for Braking Module

Article No. : 6SL3300-1AF32-5BA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :



Figure similar

Rated data	
Rated power P _{DB}	50.00 kW
Rated power, max.	250.00 kW
Activation threshold	967 V (841 V)
	adjustable via DIP switch

General technical specifications	
DC link voltage	DC 675 ... 900 V

Mechanical data	
Net weight	7.5 kg (16.53 lb)

Digital inputs	
Number	1
Voltage	24 V
Low level	-3 V ... 5 V
High level	15 V ... 30 V
Power consumption at 24 V DC, typ.	10 mA

Digital outputs	
Number	1
Voltage	DC 24 V
Load current per digital output, max.	500 mA

Connections	
-------------	--

Digital inputs	
Connection cross-section, max.	1.5 mm ² (16 AWG)

Digital outputs	
Connection cross-section, max.	1.5 mm ² (16 AWG)

PE connection	
Version on housing	M8 nut

BrakeResistor	
Connection cross-section, max.	50.0 mm ² (1 AWG)