



SINAMICS S150

MLFB-Ordering data: 6SL3710-7LG34-1AA3

Client order no.:
Order no.:
Offer no.:
Remarks:

Item no.:
Consignment no.:
Project:

Rated data:		Environmental conditions:	
Input:		Installation altitude	1000 m
Supply frequency	47...63 Hz	Coolant	Air
Supply voltage	500 V ±10%	Coolant requirement, air	1.96 m³/s
Rated input current	375 A	Min. ambient temperature	0 °C
Max. current	619 A	Max. ambient temperature	40 °C
Pulse number	6		
Energy recovery capability	Yes (4Q)		

Output:

Output voltage	500 V
Rated power (LO) in kW	250 kW
Rated power (HO) in kW	200 kW
Rated output current	410 A
Rated output current (LO)	400 A
Rated output current (HO)	367 A
Output current Max	600 A
Pulse frequency (factory setting)	1.25 kHz

Special design:

Basic data:

Efficiency η	96.00 %
Power losses ΔP	19.98 kW
Power loss including options	19.98 kW
Sound pressure level L_{pA} (1 m)	77 dB
Conductor cross section, max. (IEC)	4 x 240 mm²
Degree of protection	IP20
Width	2200 mm
Height	2000 mm
Depth	600 mm
Weight approx.	1716 kg
Frame size	H
Color, paint shade	RAL7035