

Article No. : 6SL3760-0MR00-0AA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Figure similar

Rated data	
Input	
Number of phases	3 AC
Line voltage	380 ... 480 V
Output	
Rated current	1,200.0 A
General technical specifications	
Power loss	0.106 kW

Mechanical data	
Degree of protection	IP00
Net weight	25.00 kg (55.10 lb)
Dimensions	
Width	425.0 mm (16.70 in)
Height	265.0 mm (10.40 in)
Depth	148.0 mm (5.83 in)