



Figure similar

MLFB-Ordering data 1FK7042-2AF21-1QA0

Optimum operating point		Recommended Motor Module	
Optimum speed	3000 rpm	Rated inverter current	4 A
Optimum power	0.8 kW	Maximum inverter current	8 A
Limiting data		Maximum torque	6.00 Nm
Max. permissible speed (mech.)	9000 rpm		
Max. permissible speed (inverter)	5800 rpm		
Maximum torque	10.5 Nm		
Maximum current	13.8 A		