



MLFB-Ordering data 1FK7084-3BC71-1CG2

Optimum operating point		Recommended Motor Module	
Optimum speed	2000 rpm	Rated inverter current	9 A
Optimum power	3.1 kW	Maximum inverter current	27 A
Limiting data		Maximum torque	58.40 Nm
Max. permissible speed (mech.)	6000 rpm		
Max. permissible speed (inverter)	3800 rpm		
Maximum torque	61.0 Nm		
Maximum current	28.5 A		