



MLFB-Ordering data 1FK7101-3BC71-1CA1

Optimum operating point		Recommended Motor Module	
Optimum speed	2000 rpm	Rated inverter current	18 A
Optimum power	4.3 kW	Maximum inverter current	54 A
Limiting data		Maximum torque	80.00 Nm
Max. permissible speed (mech.)	5000 rpm		
Max. permissible speed (inverter)	4000 rpm		
Maximum torque	80.0 Nm		
Maximum current	40.5 A		