



MLFB-Ordering data 1FK7103-3BC71-1CG2

Optimum operating point		Recommended Motor Module	
Optimum speed	2000 rpm	Rated inverter current	18 A
Optimum power	5.2 kW	Maximum inverter current	54 A
Limiting data		Maximum torque	108.00 Nm
Max. permissible speed (mech.)	5000 rpm		
Max. permissible speed (inverter)	3550 rpm		
Maximum torque	108.0 Nm		
Maximum current	46.5 A		