

Article No. : 1FK2104-4AK00-1MA0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :



Figure similar

| Basic motor data        |                                                           |
|-------------------------|-----------------------------------------------------------|
| Motor type              | Permanent-magnet synchronous motor, Natural cooling, IP64 |
| Motor type              | High Dynamic                                              |
| Static torque           | 1.27 Nm                                                   |
| Static current          | 2.4 A                                                     |
| Maximum torque          | 3.85 Nm                                                   |
| Maximum current         | 8.7 A                                                     |
| Maximum speed           | 8,000 rpm                                                 |
| Rotor moment of inertia | 0.3500 kgcm <sup>2</sup>                                  |
| Weight                  | 2.0 kg                                                    |

| Rated data              |           |
|-------------------------|-----------|
| SINAMICS S210, 3AC 400V |           |
| Rated speed             | 6,000 rpm |
| Rated torque            | 0.95 Nm   |
| Rated current           | 1.9 A     |
| Rated power             | 0.60 kW   |

| Encoder system |                                                             |
|----------------|-------------------------------------------------------------|
| Encoder system | Encoder AM22DQC: Absolute encoder 22 bit + 12 bit multiturn |

| Motor connection |              |
|------------------|--------------|
| Connection type  | OCC for S210 |
| Connector size   | M17          |

| Mechanical data               |                                            |
|-------------------------------|--------------------------------------------|
| Design acc. to Code I         | IM B5 (IM V1, IM V3)                       |
| Vibration severity grade      | Grade A                                    |
| Shaft height                  | 40                                         |
| Flange size (AB)              | 80 mm                                      |
| Centering ring (N)            | 70 mm                                      |
| Hole circle (M)               | 90 mm                                      |
| Screw-on hole (S)             | 6.5 mm                                     |
| Overall length (LB)           | 98 mm                                      |
| Diameter of shaft (D)         | 19 mm                                      |
| Length of shaft (E)           | 40 mm                                      |
| Length of flange diagonal (P) | 105 mm                                     |
| Shaft end                     | Fitted key                                 |
| Color of the housing          | Standard (Anthracite, similar to RAL 7016) |

