

Data sheet for SIMOTICS S-1FK2

Article No. : 1FK2204-5AK00-1MA0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Basic motor data

| | |
|-------------------------|---|
| Motor type | Permanent-magnet synchronous motor, Natural cooling, IP64 |
| Motor type | Compact |
| Static torque | 2.40 Nm |
| Static current | 4.4 A |
| Maximum torque | 7.10 Nm |
| Maximum current | 14.2 A |
| Maximum speed | 8,000 rpm |
| Rotor moment of inertia | 1.2300 kgcm ² |
| Weight | 2.9 kg |

Rated data

SINAMICS S210, 3AC 400V

| | |
|---------------|-----------|
| Rated speed | 6,000 rpm |
| Rated torque | 0.90 Nm |
| Rated current | 2.0 A |
| Rated power | 0.57 kW |

Encoder system

| | |
|----------------|---|
| Encoder system | Encoder AM22DQC: Absolute encoder 22 bit + 12 bit multiturn |
|----------------|---|

Motor connection

| | |
|-----------------|--------------|
| Connection type | OCC for S210 |
| Connector size | M17 |

Mechanical data

| | |
|-------------------------------|--|
| Design acc. to Code I | IM B5 (IM V1, IM V3) |
| Vibration severity grade | Grade A |
| Shaft height | 40 |
| Flange size (AB) | 80 mm |
| Centering ring (N) | 70 mm |
| Hole circle (M) | 90 mm |
| Screw-on hole (S) | 6.5 mm |
| Overall length (LB) | 126 mm |
| Diameter of shaft (D) | 19 mm |
| Length of shaft (E) | 40 mm |
| Length of flange diagonal (P) | 105 mm |
| Shaft end | Fitted key |
| Color of the housing | Standard (Anthracite, similar to RAL 7016) |

