



Figure similar

MLFB-Ordering data

6FC5211-0BA01-0AA4

Client order no. :

Item no. :

Order no. :

Consignment no. :

Offer no. :

Project :

Remarks :

Rated data

Input voltage DC 24 V

Power consumption, max. 30.2 W

Mechanical data

Degree of protection IP20 / UL open type

Net weight 1.50 kg (3.31 lb)

Width 48.5 mm (1.91 in)

Height 325.0 mm (12.80 in)

Depth 154.4 mm (6.08 in)

Ambient conditions

Climate class according to EN60721-3-3 Condensation and icing excluded. Low air temperature 0 °C (32 °F).

Ambient temperature

Operation 0 ... 55 °C (32 ... 131 °F)

Transport -40 ... 70 °C (-40 ... 158 °F)

Storage -20 ... 55 °C (-4 ... 131 °F)

Relative humidity

Operation 5 ... 95 %

Storage 5 ... 95 %

Transport 5 ... 95 %

Approvals

Certificate of suitability CE / UL / CSA