

## Datenblatt für SINUMERIK CompactFlash Card

Data sheet for SINUMERIK CompactFlash card

### MLFB-Bestelldaten

MLFB-Ordering data

6FC5313-5AG00-0AA2



Abbildung ähnlich / Figure similar

Kunden-Auftrags-Nr. / Client order no.:

Siemens-Auftrags-Nr. / Order no.:

Angebots-Nr. / Offer no.:

Bemerkung / Remarks:

Item-Nr. / Item no.:

Komm.-Nr. / Consignment no.:

Projekt / Project:

### Speicher / Memory

<b>Typ der Speicherkarte</b> <i>Type of memory card</i>	CompactFlash Card <i>CompactFlash card</i>
<b>Speicherkapazität</b> <i>Memory capacity</i>	2 Gbyte <i>2 Gbyte</i>

### Mechanische Daten / Mechanical data

<b>Schutzart</b> <i>Degree of protection</i>	IP20 / UL open type
<b>Nettogewicht</b> <i>Net weight</i>	0,012 kg (0,03 lb)
<b>Breite</b> <i>Width</i>	43 mm (1,69 in)
<b>Höhe</b> <i>Height</i>	3 mm (0,12 in)
<b>Tiefe</b> <i>Depth</i>	37 mm (1,46 in)

### Umgebungsbedingungen / Ambient conditions

#### Klimaklasse gemäß EN60721-3-3

*Climate class according to EN60721-3-3*

Betauung und Eisbildung  
ausgeschlossen. Niedrige  
Lufttemperatur 0 °C.  
*Condensation and icing excluded. Low air  
temperature 0 °C (32 °F).*

#### Umgebungstemperatur / Ambient temperature

<b>Betrieb</b> <i>Operation</i>	0 ... 85 °C (32 ... 185 °F)
<b>Lagerung</b> <i>Storage</i>	-40 ... 100 °C (-40 ... 212 °F)
<b>Transport</b> <i>Transport</i>	-40 ... 100 °C (-40 ... 212 °F)

#### Relative Luftfeuchte / Relative humidity

<b>Betrieb</b> <i>Operation</i>	10 ... 80 %
<b>Transport</b> <i>Transport</i>	5 ... 95 %
<b>Lagerung</b> <i>Storage</i>	5 ... 95 %

### Approbationen / Approvals

<b>Eignungsnachweis</b> <i>Certificate of suitability</i>	CE, cULus <i>CE, cULus</i>
--	-------------------------------