

Data sheet for MICROMASTER Basic Operator Panel (BOP)

Article No. : 6SE6400-0BP00-0AA1



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Screen

Display design LCD, monochrome

Mechanical data

Degree of protection IP20 / UL open type

Net weight 0.300 kg (0.66 lb)

Dimensions

Width 71.00 mm (2.80 in)

Height 80.00 mm (3.15 in)

Depth 16.00 mm (0.63 in)

Ambient conditions

Ambient temperature

Operation -10 ... 50 °C (14 ... 122 °F)

Storage -40 ... 70 °C (-40 ... 158 °F)

Transport -40 ... 70 °C (-40 ... 158 °F)

Relative humidity at 25°C during

Max. operation 95 %

Approvals

Certificate of suitability UL, CE, C-Tick (RCM)