

Data sheet for Line reactor

MLFB-Ordering data

6SE6400-3CC04-4DD0



Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data

Input

Number of phases	3 AC
Line voltage	380 ... 600 V

Output

Rated current	45.8 A
---------------	--------

Mechanical data

Dimensions

Width	275.0 mm (10.8 in)
Height	520.0 mm (20.5 in)
Depth	83.5 mm (3.3 in)
Degree of protection	IP20 / UL open type
Net weight	13.0 kg (28.7 lb)

Connections

Line side

Version	screw-type terminal
Conductor cross-section	10.00 ... 16.00 mm ² (8 ... 6 AWG)

Load side

Version	Pigtail
Conductor cross-section	16.00 mm ² (6 AWG)
Cable length	0.79 m (2.59 ft)

PE connection

Version	M8 stud
---------	---------

Standards

Compliance with standards	cURus
---------------------------	-------