

## Data sheet for braking resistor

Article No. : 6SE6400-4BD12-0BA0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :



Figure similar

### Rated data

Rated power $P_{DB}$	0.2 kW
Rated power, max.	4 kW

### General technical specifications

Resistance	160 $\Omega$
DC-link voltage, max.	900 V

### Mechanical data

Degree of protection	IP20 / UL open type
Net weight	1.6 kg (3.53 lb)
Dimensions	
Width	149 mm (5.87 in)
Height	239 mm (9.41 in)
Depth	43.5 mm (1.71 in)

### Connections

Power connection	
Version	pigtail
Cable length	0.55 m (1.8 ft)
PE connection	
Version	pigtail
Version on housing	M4 stud bolt

### Thermostatic switch

Version	Normally closed contact
Input current, max.	2.5 A
Conductor cross-section	2.5 mm <sup>2</sup> (AWG 14)