



Figure similar

MLFB-Ordering data

6SE6430-2AD31-5CA0

Client order no. :

Item no. :

Order no. :

Consignment no. :

Offer no. :

Project :

Remarks :

### Rated data

#### Input

Number of phases	3 AC
Line voltage	380 ... 480 V $\pm$ 10 %
Line frequency	47 ... 63 Hz
Rated current (LO)	33.80 A

#### Output

Number of phases	3 AC
Rated voltage	480 V
Rated power (LO)	15.00 kW / 20.00 hp
Rated current (LO)	32.00 A
Pulse frequency	4000 Hz
Output frequency for V/f control	0 ... 650 Hz

As a result of legal stipulations, a limit to 550 Hz is in production

### General tech. specifications

Power factor $\lambda$	0.95
Efficiency $\eta$	0.96

### Ambient conditions

Cooling	Fan
---------	-----

#### Ambient temperature

Operation (LO)	-10 ... 40 °C
----------------	---------------

Transport	-40 ... 70 °C
-----------	---------------

Storage	-40 ... 70 °C
---------	---------------

### Overload capability

#### Low Overload (LO)

140 % output current for 3 s, followed by 110 % output current for 57 s followed by 100 % output current for 240 s in a 300 s cycle time



Figure similar

MLFB-Ordering data

6SE6430-2AD31-5CA0

### Mechanical data

Degree of protection	IP20 / UL open type
Size	FSC
Net weight	5.70 kg
Width	185.0 mm
Height	245.0 mm
Depth	195.0 mm

### Connections

#### Motor end

Conductor cross-section	10.00 mm <sup>2</sup>
-------------------------	-----------------------

### Inputs / outputs

#### Standard digital inputs

Number	6
--------	---

#### Relay output

Number	3
--------	---

#### Analog inputs

Number	2
--------	---

#### Analog outputs

Number	2
--------	---

#### PTC/ KTY interface

Number	1
--------	---