



Figure similar

MLFB-Ordering data

6SE6430-2UD41-3FA0

Client order no. :

Item no. :

Order no. :

Consignment no. :

Offer no. :

Project :

Remarks :

Rated data

Input

Number of phases	3 AC
Line voltage	380 ... 480 V \pm 10 %
Line frequency	47 ... 63 Hz
Rated current (LO)	245.00 A

Output

Number of phases	3 AC
Rated voltage	480 V
Rated power (LO)	132.00 kW / 200.00 hp
Rated current (LO)	250.00 A
Pulse frequency	2000 Hz
Output frequency for V/f control	0 ... 267 Hz

General tech. specifications

Power factor λ	0.95
Efficiency η	0.97

Ambient conditions

Cooling	Fan
---------	-----

Ambient temperature

Operation (LO)	0 ... 40 °C
----------------	-------------

Transport	-40 ... 70 °C
-----------	---------------

Storage	-40 ... 70 °C
---------	---------------

Overload capability

Low Overload (LO)

150 % output current for 1 s, followed by 110 % output current for 59 s followed by 100 % output current for 240 s in a 300 s cycle time

MLFB-Ordering data

6SE6430-2UD41-3FA0



Figure similar

Mechanical data

Degree of protection	IP20 / UL open type
Size	FX
Net weight	116.00 kg
Width	326.0 mm
Height	1400.0 mm
Depth	356.0 mm

Connections

Motor end

Conductor cross-section	185.00 mm ²
-------------------------	------------------------

Inputs / outputs

Standard digital inputs

Number	6
--------	---

Relay output

Number	3
--------	---

Analog inputs

Number	2
--------	---

Analog outputs

Number	2
--------	---

PTC/ KTY interface

Number	1
--------	---