



Figure similar

### MLFB-Ordering data

6SL3100-0BE28-0AB0

Client order no. :

Item no. :

Order no. :

Consignment no. :

Offer no. :

Project :

Remarks :

### Electrical data

#### Input

Number of phases	3 AC
Line voltage	380 ... 480 V
Internal resistor	1440 Ω +10% -10%

### Rated data

Rated current	128 A
Power requirement (DC 24 V)	1.20 A
Switching current (as NC circuit at 250 V AC)	1.6 A
Switching current (as NC circuit at 60 V DC)	0.75 A

### Mechanical data

#### Dimensions

Width	300 mm (11.81 in)
Height	380 mm (14.96 in)
Depth	270 mm (10.63 in)

Degree of protection IP20 / UL open type

Net weight 31.90 kg (70.33 lb)

Type of construction Booksize

### General tech. specifications

Sound pressure level	68 dB
Power loss	0.49 kW

### Ambient conditions

Type of cooling	Internal air cooling
Cooling air throughput	0.17 m³/s (5.90 ft³/s)

### Standards

Compliance with standards	cURus
---------------------------	-------

### Connections

#### Line side

Version	M8 bolt
Conductor cross-section	2.5 mm² ... 120 mm² (14 ... -3 AWG) (Alternatively 2 x 50 mm²)
PE conductor	M8 Screw