



Figure similar

MLFB-Ordering data

6SL3210-5FE10-8UA0

Client order no. :

Item no. :

Order no. :

Consignment no. :

Offer no. :

Project :

Remarks :

Rated data	Ambient conditions
------------	--------------------

Input	
Number of phases	3 AC
Line voltage	380 ... 480 V +10 % -15 %
Line frequency	45 ... 66 Hz
Output	
Rated power	0.75 kW
Rated current (IN)	2.10 A
Max. output current	6.30 A

Cooling	natural convection
Installation altitude	1000 m
Ambient temperature	
Operation	0 ... 45 °C
Storage	-40 ... 70 °C
Relative humidity	
Max. operation	90 %

Inputs / outputs

Standard digital inputs	
Number	10
Digital outputs	
Number	6
Analog inputs	
Number	2
Analog outputs	
Number	2

Standards

Compliance with standards	CE, KC, cULus, EAC, C-Tick (RCM)
---------------------------	----------------------------------

Communication

Communication	USS, Modbus RTU
---------------	-----------------

Mechanical data

Degree of protection	IP20 / UL open type
Frame size	FSA
Net weight	1.85 kg
Width	80.0 mm
Height	180.0 mm
Depth	200.0 mm