



Figure similar

MLFB-Ordering data

6SL3210-5FE12-0UA0

Client order no. :

Item no. :

Order no. :

Consignment no. :

Offer no. :

Project :

Remarks :

Rated data		Ambient conditions	
<b>Input</b>		<b>Cooling</b>	Fan
Number of phases	3 AC	<b>Installation altitude</b>	1000 m
Line voltage	380 ... 480 V +10 % -15 %	<b>Ambient temperature</b>	
Line frequency	45 ... 66 Hz	<b>Operation</b>	0 ... 45 °C
<b>Output</b>		<b>Storage</b>	-40 ... 70 °C
Rated power	2.50 kW	<b>Relative humidity</b>	
Rated current (IN)	7.80 A	<b>Max. operation</b>	90 %
Max. output current	23.40 A	<b>Standards</b>	
<b>Inputs / outputs</b>		<b>Compliance with standards</b>	CE, KC, cULus, EAC, C-Tick (RCM)

### Standard digital inputs

Number 10

### Digital outputs

Number 6

### Analog inputs

Number 2

### Analog outputs

Number 2

### Mechanical data

Degree of protection IP20 / UL open type

Size FSB

Net weight 2.45 kg

Width 100.0 mm

Height 180.0 mm

Depth 220.0 mm