



Figure similar

Data sheet for SINAMICS Control unit CU230P-2 PN

Article No. : 6SL3243-0BB30-1FA0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Electrical data

Operating voltage via

The Power Module	DC 24 V
External power supply	DC 20 ... 29 V
Max. power consumption	0.50 A
Power loss	5.50 W

Communication

Communication PROFINET, EtherNet/IP

Inputs / outputs

Standard digital inputs

Number	6
Switching level: 0→1	11 V
Switching level: 1→0	5 V

Fail-safe digital inputs

Number	0
--------	---

Digital outputs

as relay changer

Number	2
Output (inductive load)	DC 250 V, 2 A
Output (resistive load)	DC 30 V, 0.5 A

as relay make contact

Number	1
Output (resistive load)	DC 30 V, 0.5 A

Analog / digital inputs

Number	2 (Differential input)
--------	------------------------

Analog outputs

Number	2 (Non-isolated output)
--------	-------------------------

Closed-loop control techniques

V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	Yes
Torque control, with encoder	No

Ambient conditions

Ambient temperature

Operation	-10 ... 60 °C (14 ... 140 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)

Relative humidity

Max. operation	95 %
----------------	------

Connections

Signal cable

Conductor cross-section	0.15 ... 1.50 mm ² (AWG 24 ... AWG 16)
-------------------------	--

Mechanical data

Degree of protection	IP20 / UL open type
Net weight	0.61 kg (1.34 lb)

Dimensions

Width	73.0 mm (2.87 in)
Height	199.0 mm (7.83 in)
Depth	65.5 mm (2.59 in)

Standards

Compliance with standards	CE, UL, cUL, RCM, SEMI F47
CE marking	Low-voltage directive 2014/35/EC