

[illegible]

- | | | | | | | |
|---|--------------|---------------------|-------------|---|----------|--------|
| Tolerance
DIN EN 50347
Untolerated Dimensions- ISO 2768v / IS2102v | Surface | Material | Weight
- | Scale
 mm | | |
| FS..315S; Const.:1MB3
1LE7501-3AC03-5AA4
- | Author | Dimensional drawing | | | | |
| | Creator | | | | DTK | |
| | Approval | | | | | |
| | Department | | | | | |
| | Change Order | MLFB | Doc Type | | | |
|  | Doc State | 5/22/24 | Item No | Paper Size | A4 | |
| | Revision | Index | RS | Doc No | Language | en |
| © Siemens AG 2023 | Project No | - | Ref No | - | Sheet | 1 of 1 |

SIEMENS