

[illegible]

- | | | | | |
|---|---------------------------------|---------------------|---------------------------|---|
| Tolerance
DIN EN 50347
Untolerated Dimensions- ISO 2768v / IS2102v | Surface | Material | Weight
- | Scale
 mm |
| FS.:71M; Const.:IMB3
1LE7503-0CC32-3AA4
- | Author | Dimensional drawing | | |
| | Creator
<div>DTK</div> | | | |
| | Approval | | | |
| | Department | | | |
| | Change Order | | | |
|  | Doc State
<div>5/22/24</div> | Item No | Doc Type | Paper Size
<div>A4</div> |
| | Revision
<div>Index RS</div> | Doc No | Language
<div>en</div> | |
| | © Siemens AG 2023 | Project No - | Ref No - | Sheet 1 of 1 |