


Transmittal, reproduction, dissemination and/or editing of this document as well as the use of its content for purposes not intended by the manufacturer without express authorization are prohibited. Offenders will be held liable for payment of damages. All rights created by patent grant or registration of a utility model or design patent are reserved.



- 1) Protected centre hole M10x24
- 2) Relief groove as per DIN509 / IS:3428
- 3) Measured across screw heads

Tolerance DIN EN 50347 Untolerated Dimensions- ISO 2768v / IS2102v	Surface	Material	Weight	Scale
			-	mm
FS.:100L; Const.:IMB3 1LE7503-1AB43-5AA4	Author	Dimensional drawing		
	Creator			
-	Approval	DTK		
	Department			
	Change Order	MLFB		Doc. Type
	Doc. State	5/21/24	Item No	Paper Size
SIEMENS	Revision	Index	RS	Language
	Ref No	-	Ref No	-
© Siemens AG 2023	Project No	-	Ref No	-